



Chemical protection

BUTOFLEX 650

ultra-comfort wear

Ultimate specific chemical resistance

SPECIFIC ADVANTAGES



Comfort

- Exceptional comfort; the first butyl glove on the market with a fabric inner lining
- Unrivalled flexibility and dexterity



Skin protection

- Ultimate specific chemical resistance, for very corrosive acids, ketones, esters and amine derivatives



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting

INDUSTRIES

- Mechanical industry
- Chemical industry
- Cosmetics and Pharmaceutical industry

APPLICATIONS

- Metal treatment and degreasing
- Formulating paints, varnishes, resins and inks
- Handling and repackaging chemicals
- Sampling chemicals
- Handling in laboratories



CHEMICAL PROTECTION
TYPE A

EN388



1121X

EN ISO 374-1



TYPE A
ABCILMNOS

EN ISO 374-5



CATEGORY 3

DEXTERITY



0334

EN ISO 21420:
5/5



Chemical protection

BUTOFLEX 650

ultra-comfort wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
1 1 2 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
	A: Methanol
	B: Acetone
	C: Acetonitrile
	I: Ethyl acetate
TYPE A	L: Sulphuric acid 96%
	M: Nitric acid 65%
	N: Acetic acid 99%
	O: Ammonia 25%
	S: Hydrofluoric acid 40%
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Textile support Mapa Technology
Exterior finish	Embossed texture
Material	Butyl
Cuff characteristic	Feston Cuff
Colours	Black
Length (cm)	35
Thickness (mm)	1.45
European sizes	7 8 9 10 11
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	2.0E+5 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	6.7E+8 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 6 pairs/carton
-----------	------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/10/18/2133
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France

Edit 07/01/2025