

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION AUG ,2005.



© COPYRIGHT 2005 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
		C		ECR-07-011423	15/05/07	AM	FWK

NOTES:

- ELECTRICAL DATA: CONTACT RESISTANCE: 10 mOhm MAX
INSULATION RESISTANCE: 100 MOhm MIN at 500VDC
CURRENT RATING: 5 AMPS
BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE
- ENVIRONMENTAL: OPERATING TEMPERATURE: -20°C TO +80°C
SEALING REQUIREMENTS: IP67
- PROD SPEC: 108-3641
- PACKAGING: 107-3334
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	BLACK	1
3	PIN CONTACT	BRASS	0.15µm GOLD PLATED OVER NICKEL	3
4	3 CORE CABLE (CORES 22AWG TO UL2464)	PVC JACKET UV RESISTANT	BLACK	1



10000	500mm	M12 STRAIGHT MALE CONNECTOR 10.0m CABLE	1838236-5
7000	350mm	M12 STRAIGHT MALE CONNECTOR 7.0m CABLE	1838236-4
5000	250mm	M12 STRAIGHT MALE CONNECTOR 5.0m CABLE	1838236-3
3000	150mm	M12 STRAIGHT MALE CONNECTOR 3.0m CABLE	1838236-2
2000	100mm	M12 STRAIGHT MALE CONNECTOR 2.0m CABLE	1838236-1
DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19AUG05 H M RAGHAVENDRA	tyco Electronics Tyco Electronics Corporation Bideford, UK, EX39 4HE											
DIMENSIONS: mm		CHK 15DEC05 F.WHEELER-KING												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 15DEC05 F.WHEELER-KING	M12 STRAIGHT MALE CONNECTOR 3 POSITION, PVC CABLE											
<table border="1" style="font-size: small;"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC			± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES
0 PLC	± -													
1 PLC	± -													
2 PLC	± -													
3 PLC	± -													
4 PLC	± -													
ANGLES	± -													
MATERIAL -		FINISH -	APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-1838236	RESTRICTED TO -							
CUSTOMER DRAWING			WEIGHT -	SCALE NTS	SHEET 1 OF 1	REV C								