



kingston.com/flash

CANVAS GO! PLUS microSD

Capturing Adventure on the Go!

Kingston's Canvas Go! Plus microSD is for adventurers who are always on the go chasing the perfect moment to capture. With superior transfer speeds of up to 170MB/s¹, the Canvas Go! Plus microSD card accelerates your workflow and efficiency so that you'll have more time to take your creativity onto the next adventure. With U3 and V30 speed performance, shoot stunning 4K Ultra-HD videos without worrying about slow speeds and dropped frames, or shoot fast-action photos that are seamless and consistent. The Canvas Go! Plus microSD supports A2 Application Performance Class to expedite your workflow with faster application performance on smartphones and tablets. An optional SD adapter provides added versatility for use with SD-compatible devices. View the world as your canvas and take your creativity and inspiration on the road with the Canvas Go! Plus microSD.

- › Superior transfer speeds of up to 170MB/s¹
- › Ideal for action cameras, drones and Android devices
- › U3 & V30 speed performance
- › Supports A2 app performance class
- › Durable

FEATURES / BENEFITS

Superior speeds — Transfer and capture content faster in Full HD & 4K UHD with transfer speeds of up to 170MB/s.¹

Ideal for action cameras and drones — High speeds with UHS Speed Class 3 (U3) & Video Speed Class 30 (V30) ratings.

Durable — For your peace of mind, the card has been extensively tested and proven to be waterproof, temperature proof, shock and vibration proof, and X-ray proof.³

Supports A2 app performance class — Expedite your workflow with faster application performance.

SPECIFICATIONS

Capacities²

64GB, 128GB, 256GB, 512GB

Standard/Class

Class 10, UHS-I, U3, V30, A2

Performance¹

170/70MB/s read/write (64GB)

170/90MB/s read/write (128GB-512GB)

Dimensions

11mm x 15mm x 1mm (microSD)

24mm x 32mm x 2.1mm (with SD adapter)

Format

exFAT

Storage temperature

-40°C~85°C

Operating temperature

-25°C~85°C

Voltage

3.3V

Warranty/support

lifetime



KINGSTON PART NUMBERS

Card (SD adapter included):	Card (SD adapter not included):
SDCG3/64GB	SDCG3/64GBSP
SDCG3/128GB	SDCG3/128GBSP
SDCG3/256GB	SDCG3/256GBSP
SDCG3/512GB	SDCG3/512GBSP

1. Based on internal testing; performance will vary based on host device. Engineered with proprietary technology to reach read speeds beyond UHS-I 104MB/s specification, up to 170MB/s. Full performance requires MobileLite Plus microSD Reader.

2. Some of the listed capacity on a Flash storage device is used for formatting and other functions and is thus not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's Flash memory guide at kingston.com/flashguide.

3. IEC/EN 60529 IPX7-certified for protection against continual water submersion for up to 30 minutes at a depth of up to 1m. Withstands temperature range from -25 °C to 85 °C. Based on MIL-STD-883H, METHOD 2002.5 military standard test method. Protected against X-ray exposure based on ISO7816-1 guidelines.

