

HPP V4 EI-PFT metal housing with clip



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 595 0031
Specification	HPP V4 EI-PFT metal housing with clip
HARTING eCatalogue	https://harting.com/09455950031

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Easy Install With board locks With integrated seal

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead Nickel
--------------------------------------	----------------

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	22.8 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140061736
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466