



AS SC-S246 TL20



## AS SC-S246 TL20

E1441344

Assortment Box ov 135pcs, Releasable, Terminal Blocks



### Product Properties:

Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	32 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	2-5 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Green

### Dimensions:

Max. AWG-size	12
Min. AWG-size	Other
Nominal cross section (device side)	0.2-4 mm <sup>2</sup>
Nominal cross section (installation side)	0.2-4 mm <sup>2</sup>
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.2-4 mm <sup>2</sup>
Width	200 mm
Height	41 mm
MOQ	1 .
Unit	pcs
Nominal cross section	0.2-4 mm <sup>2</sup>
Length	255 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
--------------------------	-----

### **Compliance:**

REACH	No SVHC (Latest. 04 Feb 2026)
-------	-------------------------------

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Assortment Boxes
Search Description	SORTIMENT SKARVKLÄMMOR, 135ST, ENR2024V
Alternative SKU	ASSC-S246TL20
E-no	E1441344

### **Logistic information:**

Barcode	733117641532
Country of origin	CN
E-no	E1441344
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC-S246 TL20
Taric code	85369010
Unit	pcs

