

7.2v Li-ion Cordless Impact Driver



Satisfying the professional's needs

TD021DSE

Electric Brake	1
Variable Speed Control	1
Voltage	7.2 v
Standard Bolt	M3-M8
Max Torque	22 Nm
No Load Speed	0 - 2300 rpm
Battery Type	Lithium-ion
Charging Time	30 min
Vibration: Fastening Bolt	6.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Net weight	0.54 kg
Reversing Function	1
Driving Shank	6.35mm (1/4") Hex



- LED Job light (single-light, before glow function) for illuminated operation
- Powered by Li-ion Battery BL7010 (7.2v - 1.0Ah)
- Variable speed control, enabling precision adjustment of rotational speed for careful screw driving.
- With reversing function.
- Easy to turn on/off, adjust rotational speed and reverse rotation because the switch is located ergonomically; on the side of the housing, not on the top.

Details correct as of: 8-10-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.