

BS 18 Li (602116530) Cordless Drill / Screwdriver

2x18V/2Ah Li-ion; Charger SC 60 Plus (220-240 V / 50 - 60 Hz); Plastic Carry Case

Order no. 602116530

EAN 4007430247230



Product may differ from Image

- Integrated working light to illuminate the contact area
- Battery packs with capacity display for checking the charge status
- Ultra-M technology for highest performance, gentle efficient charging, optimum energy utilisation and long service life
- 3-year warranty on battery packs thanks to Ultra-M technology

Technical data

Characteristics

Type of battery pack	Li-ion
Battery pack voltage	18 V
Capacity of battery pack	2 Ah
Maximum torque - soft	24 Nm / 212 in-lbs
Maximum torque, hard	48 Nm / 425 in-lbs
Adjustable torque	0.8 - 5 Nm // 7 - 44 in-lbs
Drill Ø steel	10 mm / 3/8 "
Drill-Ø soft wood	20 mm / 3/4 "
No-load speed	0 - 450 / 0 - 1650 /min
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight (including battery pack)	1.5 kg / 3.3 lbs

Vibration

Drilling in metal	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²
Screwdriving without impact	2.5 m/s ²
Uncertainty of measurement K	1.5 m/s ²

Noise emission

Sound pressure level	73 dB(A)
Uncertainty of measurement K	3 dB(A)

Scope of delivery

- Keyless chuck
- 2 Li-Power battery packs (18 V/2.0 Ah)
- Charger SC 60 Plus
- Plastic carry case