



R-065

Cut-resistant impact gloves, with a TPR design and knit shell for dexterous comfort



Impact

Abrasion Protection



Cut



Light Duty

Cut-resistant impact gloves, with a TPR design and knit shell for dexterous comfort

- **Specialized defenses:** Thank to a breathable knit shell developed with RINGERS® F3 Technology™, these impact-resistant gloves combine advanced, EN/ANSI-certified cut resistance with excellent comfort and dexterity
- **Added protection:** In addition to their knit shell, RINGERS® R065 safety gloves boast a patented TPR (thermoplastic rubber) design and half-dipped nitrile palm, ensuring ANSI/ISEA-compliant impact protection
- **Enhanced features:** Their high-visibility design, with touchscreen-compatible thumb tips, index and middle fingers, enhance user-friendliness, while improving workplace safety
- **Improved grip:** Their half-dipped coating features a palm with a sandy finish, offering wearers secure grip in wet and dry environments, for greater overall hand safety



Industries

- Manufacturing
- Mining
- Oil and gas
- Construction
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Applications

- Makeup and breakout tools
- Running tools into the wellbore
- Engagement and release of drill string slips
- Preparation of site - set-up and disassembly of tool string
- General pumping work
- Operating of heavy machinery
- Equipment maintenance and repair
- Pipe handling
- Handling parts with sharp, rough edges
- Scaffolding
- Loading and hauling
- Assembling and mounting components



R-065

Cut-resistant impact gloves, with a TPR design and knit shell for dexterous comfort

Key Features

- **Breathable knit shell:** Cut resistance, dexterity and comfort
- **TPR material:** For protective gloves that ensure impact protection
- **Touchscreen compatibility:** Enhanced safety and usability

Technologies



Touchscreen Compatible

Performance Standards & Regulatory Compliance



EN388: 2016



4X43EP

EN 407



X1XXXX

ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R065	Finishing: Dipped Coating Material: Nitrile Liner Material: HPPE Cuff Style: Knitwrist	13	7, 8, 9, 10, 11, 12, 13	Red	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2024 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

