



tesa® 51128

Product Information



Soft Tensilised Polypropylene tape

Product Description

tesa® 51128 is a tensilised polypropylene strapping tape with a special solvent-free natural rubber adhesive system.

Product Features

- It does not damage the surfaces of typical printed or labelled carton boxes after its removal.

Application Fields

Securing of pallets loaded with printed or labelled carton boxes.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-------------------|-------|
| • Backing | MOPP | • Total thickness | 60 µm |
| • Type of adhesive | natural rubber | | |

Properties/Performance Values

- | | | | |
|-----------------------|----------|-----------------------------|-----|
| • Elongation at break | 30 % | • No discoloration | yes |
| • Tensile strength | 106 N/cm | • Residue-free removability | yes |

Adhesion to Values

- | | |
|---------|--------|
| • Steel | 1 N/cm |
|---------|--------|



tesa® 51128

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=51128>