



GPO 11-180 S Coded Professional Polisher

COVER ON THE GEAR HOUSING

Extra protection against scratches and heat thanks to gear housing cover

AIR INLET FILTER

Reliable and durable with air inlet filter



ERGONOMIC DESIGN

High on comfort with low-weight, ergonomic design and convenient speed dial switch

GOOD PERFORMANCE IN VIBRATION AND NOISE

Less fatigue thanks to low vibrations and low noise



180mm backing pad



180mm sponge pad



Auxiliary handle

- 1 Good performance in vibration and noise, less fatigue thanks to low vibrations and low noise
- 2 Good polishing performance 1100 W power and supports up to 180 mm polishing pad sizes
- 3 High on comfort with low-weight, ergonomic design and convenient speed dial switch



Description	Part No.	EAN
Polisher GPO 11-180 S	06013A2370	4053423845334

Technical Information		
Input power	W	1,100
Speed range	rpm	900 – 3,800
Disc size	mm	180
Spindle	-	M14, 5/8" for G version
Vibration	m/s ²	2.3
Noise	dB(A)	87
Soft start	-	✓
Overload protection	-	✓
Tool Dimensions (Length x Width x Height)		Mm 440 x 259 x 128
Weight (excl. Battery)		Kg 2.1



Powered by **BOSCH**



¹With online registration
www.bosch-professional.com/pro360