


SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PVC, black RAL 9005, shielded, free cable end, on Socket angled M12, coding: A, cable length: 10 m

Commercial data

Item number	1402564
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	AF1CKA
GTIN	4046356623759
Weight per piece (including packing)	587.5 g
Weight per piece (excluding packing)	567 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	No

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket angled M12
Number of positions	5
Coding type	A


SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>

Cable/line

Cable length	10 m
PVC black [PVC]	
Dimensional drawing	
Cable weight	55 kg/km
Number of positions	5
Shielded	yes
Cable type	PVC black [PVC]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	5x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.35 mm ±0.02 mm
External cable diameter	5.90 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material, filler	PVC
Material wire insulation	PVC
Single wire, color	brown, white, blue, black, gray
Thickness, insulation	≥ 0.23 mm (Core insulation) ≥ 0.76 mm (Outer cable sheath)
Overall twist	5 wires around filler to the core
Optical shield covering	85 %
Max. conductor resistance	≤ 58 Ω/km (at 20 °C)
Insulation resistance	≥ 10 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	59 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>


Drawings

Circuit diagram



Contact assignment of the M12 socket

Schematic diagram




Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable

1402564

<https://www.phoenixcontact.com/in/products/1402564>

Dimensional drawing



M12 x 1 socket, angled, shielded

SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-10,0-PVC/M12FR SH VA - Sensor/actuator cable



1402564

<https://www.phoenixcontact.com/in/products/1402564>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in