



ENGLISH

Datasheet

RS Pro Distance Meter - RSILDM-150H

RS Stock No:126-8822

Accuracy	± 1.5 mm
Battery Life	Up to 8000
Display Type	LCD
Imperial or Metric	Both
Laser Class	Class 2
Laser Wavelength	635 nm
Measurement Range	0.05 to 150 m
Model Number (p)	RSILDM-150H
Power Source	Battery
Weight	203 g



Features and Benefits

- Area, Volume Calculations
- Indirect Measurement Using Pythagoras
- Indirect Measurement Using Tilt Sensor
- Angle Measurement Using Tilt Sensor ($\pm 65^\circ$)
- Addition/Subtraction
- Continuous Measurement
- Last 20 measurements stored
- Min/Max Distance Tracking
- Timer (self-triggering)
- Laser Continuous
- Stake-out Function
- Display Illumination and Multi-line Display
- Multifunctional End piece
- Tripod Thread
- Bluetooth with APP Support

