

/ MACSOLE X //



MX 500

Art. Nr.: 63973

EN ISO 20345: 2011 – S3 HI HRO SRC

Sizes: 37 - 48

APPLICATIONS //

oil & gas, off-shore, construction, outdoor work in humid conditions, heavy industry, chemical

TECHNICAL SPECIFICATIONS //

sole: PU/rubber, excellent grip, oil, hydrocarbon and chemical resistant, self-cleaning sole profile, excellent shock absorption, injection molded PU scuff cap, resistant to contact heat up to 300°C

upper: water resistant full grain leather, padded tongue and collar, closure system with non-metallic eyelets and zip, reflective piping and insert

lining: 3D mesh, excellent breathability, quick drying

toe cap: metal free

penetration resistant midsole: metal free

hygienic insole: anatomically shaped hygienic insole with heel shock absorber

weight: 840 g in size 42