



ENGLISH

Datasheet

RS Pro Air Screwdriver

RS Stock No: 137-0887

RS Pro Air Screwdriver features a magnesium body, incorporating a lightweight feel and high-power output. Ergonomic grip design for improved manoeuvrability and rear exhaust to minimise the discomfort of exhaust air. Offers a thumb lever to switch drive direction with one finger. Durable high performance motor with high balance and maximised output speed for precision work without vibration.



Features and Benefits

- Maximum Torque 12 Nm
- Externally adjustable torque setting range from 0 to 12 in 1 Nm increments
- Durable 1/4 in. HEX bit holder
- Forward and Reverse mode
- Rear exhaust through handle
- Feather trigger mechanism
- One finger forward/reverse shift

SPECIFICATIONS

Size	1/4 Hex
Maximum Torque	12 Nm
Vibration	0.08 m/s ²
Sound	85.1 dBa
Free Speed	1,800 rpm
Weight	2.77 lb / 1.23 kg
Length	215 mm
Air Inlet Thread Size	1/4 in
Minimum Hose Size	3/8 in / 10 mm
Average Air Consumption	5 cfm / 140 l/min