

Datasheet

RS Pro 3 Channel Digital DIN Rail Time Switch Measures Hours, 110 → 240 V ac

RS Stock No: **896-6888**



Product Details

RS Pro time switch with 3 channel, supports 12/24 h display formats. This digital DIN rail has a supply voltage of 110 to 240 V ac. This astronomical switch is built-in a compact design and is ideal for outdoor and street lighting applications. The time switch features easy manual override and keypad lock.

Features and Benefits

- 35 mm wide
- 3 lines text LCD
- DIN rail mounting
- Latitude/longitude precise to the minute with time zone
- Sunrise/sunset or twilight rise/set trigger modes
- Easy programming and navigation
- DST, offset, Off hours, weekly Off features
- 12/24 hours display format
- 6 years battery reserve
- 110-240 V ac supply voltage



ENGLISH

Specifications:

Units Measured	Hours
Battery Life	6 yr
Depth	65 mm
Height	90 mm
Number of Channels	3
Contact Configuration	CO
Segment Length	1 min
Supply Voltage	110 to 240 V ac
Type	Digital
IP Rating	IP20, IP40
Number of Operating Modes	3
Power Consumption	6 VA