

NEW iSpector Pocket 500



3.7V 1200mAh, 4.4Wh, Li-ion

MODES Work Light: High | Low
Torch



2.5hrs charging time



155.6 x 35 x 22mm



97g

CODE NSI-SPECTORPOCKET-500

Supplied with Type C USB charging cable

Optional Accessories:

UK or EU adaptor: CH-USB-UK/EU

12/24V Vehicle charger: CHIC3.7-LI-ION

Narrow
Torch beam

Wide work
Light beam

Battery status
Indicators

180°

Rotational stand

PORTABLE WORK LIGHT WITH ADJUSTABLE STAND & MOUNTING OPTIONS

Compact, rechargeable inspection light with dual light modes, ideal for garages, workshops, and DIY tasks. Its lightweight, fold flat design and strong magnetic base enable hands free use in tight spaces.

- Wide work light and narrow inspection torch
- Adjustable kickstand for elevated positioning
- Magnetic base + integrated hanging hook
- Fold-flat design for easy transport and storage
- Waterproof and shockproof (IK07) housing



Scan to find
out more

