



SPECIFICATIONS					
NYLON OR TPU					
TPU/YELLOW					
BRASS/GOLD					
BRASS/NICKEL					
4.0 A					
250 V					
TPE/GRAY					
POLYESTER ELASTOMER					
3x22 AWG					
-40°C to +105°C (-40°F to +221°F)					
MEETS NEMA 1,3,4,6P AND IEC IP68					





ALL LENGTHS	TOLERANCE *				
OTDID I ENIOTI I	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER				
STRIP LENGTH	TOLERANCE *				
0-7mm	±0.5mm				
8-29mm	±1.0mm				
30-49mm	±2.0mm				
50-69mm	±3.0mm				
70-100mm	±4.0mm				
OVER 100mm	±5.0mm				
* UNLESS OTHERWISE SPECIFIED					

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

- 1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- 2. "/S101" DESIGNATES FLEXLIFE-20 AND CTRACK CABLE.

K	UPDATE CABLE DIAMETER PER ECO	KMY	04/15/14	44671
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		RCH Inc	3000 CAMPUS MINNEAPOLIS, MM 1-800-544- (763) 553-7 (763) 553-0 turck.com	N 55441 7769 7300 0708 fax
MATERIAL		DRFT CBM	DATE 10/09/00	DESCRIPTION	* /0101	
	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0	WK 4T-	*/5101	
	DRAWING ARE FOR REFERENCE ONLY	UNIT OF ME	ASUREMENT			I 55.
FINISH	CONTACT TURCK FOR MORE	MILLIMETE	ER [INCH]	IDENTIFICATION NO.		REV K
+	INFORMATION	DO NOT SCALE	THIS DRAWING	FILE: 777000698	SHEET	1 OF 1