



Datasheet

ENGLISH

Stock No: 139-098

RS Pro 5 Core Black PVC Industrial Cable



Image representative of range

Product Details

Rigid cables U 1000 R2V

These rigid cables may be used in low-voltage energy or remote control installations in semi-industrial and industrial applications.

Typical applications: power supply for lighting, electrical devices, motors, electrical connections, risers, etc.

Not recommended in areas that are flooded for more than two months of the year or in trenches forming drains.



ENGLISH

Conductors	Section	Current (A)	Voltage drop Cos. Φ 0.8 (V / A / Km)	Weight kg / km
2X	1.5 mm	24	24.2	125
3G	1.5 mm	22	21	145
	2.5 mm	30	12.8	185
4G	1.5 mm	22	21	170
	2.5 mm	22	12.8	225
5G	1.5 mm	22	21	200
	2.5 mm	30	12.8	270
7G	1.5 mm	19.5	21	205

X: cable without green / yellow
G: cable with green / yellow

Approvals

NC 32-201.

Specifications:

Number of Cores	5
Cross Sectional Area	1.5 mm ²
Length	50m
Outer Diameter	11.2mm
Current Rating	22 A
Sheath Colour	Black
American Wire Gauge	15 AWG
Sheath Material	Polyvinyl Chloride PVC
Cable Shape	Multicore
Drain Wire	Yes
Minimum Operating Temperature	-25°C
Insulation Material	XLPE
Maximum Operating Temperature	+60°C