


Black Elastic Rubber Trolley Wheel 150mm, 300kg

Black Elastic Rubber-tyred wheel

PRODUCT

Article number

55-511-150B20



Product Details

Wheel Rim : lightweight aluminium alloy, reinforced safety design

Tyre : solid, black elastic rubber, bonded to the rim.

Hub : symmetrical, with two precision ball bearings.

Specifications

Wheel Diameter - ØD ± 1%	150 mm
Hub Type	two ball bearings
Hub Length T1	60 mm ±1
Width of Tread T2	50 mm ±1
Width of Tread-on floor T3	50 mm ±1
Axle Hole Ø d	Ø 20 mm
Hardness of tread A ±4	A 75 Shore
Load capacity	300 Kg
Temperature	-20 / +60 °C
Weight	1,04 Kg

TECHNICAL DATA

Applications :

Flexible materials handling for heavy loads on uneven surfaces.

Resilient with a low starting effort.

Lightweight wheel, resistant to wear and to side impacts.

Quiet in use. Reduce shock and vibration.

Suitable for trolleys on outdoor or industrial floors (factory, warehouse, truck transport,...).

Towable by mechanized vehicle (max.speed 4Km/h)