

5904VA/T
Assortment of 102 tools in foam trays

Car repair

		art.
	059040416	5904VA/T



- n. 21 **42**: combination wrenches 6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- n. 8 **55**: double open end wrenches 6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22 mm
- n. 9 **96/SC9**: offset hexagon key wrenches \odot 1,5÷10 mm
- n. 6 **96T**: offset hexagon key wrenches \odot 2-2,5-3-4-5-6 mm
- n. 8 **952**: T - handle wrenches with swivelling socket \odot 7-8-10-12-13-14-17-19 mm
- n. 19 **920A**: 1/2" square drive hexagon sockets \odot 10-11-12-13-14-15-16-17-18-19 20-21-22-23-24-26-27-30-32 mm
- n. 1 **920/21**: 1/2" drive extension bar 125 mm
- n. 1 **920/22**: 1/2" drive extension bar 255 mm
- n. 1 **920/25**: 1/2" drive universal joint
- n. 1 **920/42**: 1/2" drive sliding T-handle 305 mm
- n. 1 **920/55**: 1/2" drive reversible ratchet ⊗
- n. 1 **1084BM**: Heavy-duty diagonal cutting nippers ∇ 160 mm
- n. 1 **1150BM**: combination pliers bright chrome-plated, bi-material handles \equiv 180 mm
- n. 1 **1166BM**: Extra-long needle nose pliers \bullet 160 mm
- n. 1 **1032**: circlip pliers straight, internal \odot 180 mm
- n. 1 **1034**: circlip pliers bent, internal \odot 170 mm
- n. 1 **1036**: circlip pliers straight, external \bullet 175 mm
- n. 1 **1038**: circlip pliers bent, external \bullet 175 mm
- n. 1 **1052**: self - locking pliers 240 mm
- n. 1 **1048N**: slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 7 **1260**: screwdrivers for slotted head screws \bullet 2,5x50 -3x75 - 3,5x100 - 4x125 -5,5x100 - 5,5x150 - 6,5x150 mm
- n. 6 **1262**: screwdrivers for cross head Phillips® screws \oplus PH0x60 - PH0x100 - PH1x80 PH1x120 - PH2x100 - PH2x150 mm
- n. 2 **35**: flat chisels, ribbed type 100-200 mm
- n. 1 **1370**: engineer's hammer 300 g
- n. 1 **1390**: soft face hammer \varnothing 35 mm
- n. 1 **VP5**: empty thermoformed tray