

EL170DDR

Heavy Industrial chukka boot



Open cell
PU footbed

Technology

DDR



Injected dual density rubber sole



Features

Standard	EN ISO 20345:2011
Category	S3 CI HI HRO SRC
Code	EL170DDR
Product type	Safety boot
Colour	Black
Size range	UK sizes 3 - 13 EU 36 - 48
Weight	775gr
Upper	Breathable Full Grain Cow Hide Leather (1.8 – 2.2mm)
Inner lining	Abrasion Resistant Moisture Wicking Textile
Safety features	Stainless Steel Toe Cap, resistant to 200J Stainless Steel Protective Midsole – Min. 1100N

Additional features

Injected Ridged Rubber Cap for extra strength and durability.

Soling technology

Lightweight Injected Dual Density Rubber/Rubber, Flexible soling system with antistatic properties, shock absorption, heat resistance to 300°C and SRC rated slip resistance.

Insole technology

Moisture wicking, breathable and washable
Open Cell PU Footbed

