


## LS SERIES

## FLEXIBLE LED LIGHTING STRIPS

Technical Information	Colour		Colour Temp (White only)	Light Output Lumens/m	Part Number
• LED: SMD3528 60LED/M		Cool White	5500 -7000K	550	LSCW6245MIP65RS
<ul> <li>Voltage: 24VDC</li> <li>Current: 600mA (per metre)</li> <li>Max consumption: (W/m) power 4.8</li> <li>Dimensions: 10mm x 5000mm (5 Metre Roll)</li> <li>Beam angle: 120°</li> </ul>		White	4000 -4500K	450	LSNW6245MIP65RS
		Warm White	2700 -3200K	400	LSWW6245MIP65RS
		Red	N/A	240	LSR6245MIP65RS
		Blue	N/A	40	LSB6245MIP65RS
Sealed up to IP65 Crystal Resin					



When mounting on a metallic or otherwise conductive surfaces, there needs to be

Caution needs to be taken after cutting the strip that exposed ends are insulated.

electrical isolation points between strip and the mounting surface.

VOYC1603R3A-RS