

611626090

# Aluminium Enclosure Standard unpainted 160 x 260 x 91 mm

Aluminium Enclosure Standard unpainted
160 x 260 x 91 mm

Declaration of Conformity

Technical Drawing | 3D Data | Assignmentplan | Terminal mounting

## Technical data

| | |
|---|---|
| Height | 160 mm |
| Width | 260 mm |
| Depth | 91 mm |
| Material | Aluminium |
| Material quality | DIN EN 1706 EN AC-AlSi 12 (Fe) |
| Colour | Aluminium, unpainted |
| Ingress protection | IP66 |
| Degree of protection norm | EN 60529 |
| Impact strength | IK09 |
| Temperature min. | -30 °C |
| Temperature max. | 90 °C |
| Seal material | CR-(Chloropren) |
| Flame spread, sideways | HL 3 |
| Rate of heat dispersion | HL 3 |
| Smoke gas concentration | HL 3 |

## Commercial data

| | |
|---|---|
| Country of origin | DE |
| Order unit | 1 Piece |
| Customs tariff number | 85369095 |
| Weight | 2.16 kg |
| GTIN | 4250157900241 |

## ETIM Classification

| | |
|---|---|
| ETIM 8 | EC000058 |

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

## Accessories



100110110
Mounting plate for 01.162609



100220010
Hinge internal / Steel



100270010
Hinge internal / grey



100311020
Outer bracket fastening set M6



100614240
DIN rail 35/7,5 for xx.162609



100620050
Earth rail 01.162609