

Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	1P + N
[I _{th}] conventional free air thermal current	25 A
I ² t on activation	200000 A ² .s
Number of cables	2 cable(s) 4 mm ² at 105 °C
Width	54 mm
Height	190 mm
Depth	61 mm





Complementary

[U _i] rated insulation voltage	690 V conforming to IEC 60439-1
Electrical connection	Connector
9 mm pitches	6
Net weight	0.23 kg

Environment

Standards	IEC 60439
Product certifications	DNV[RETURN]LROS (Lloyds register of shipping)[RETURN]CSA[RETURN]UL

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins