


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [each]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA11-A THRU PCA11-Z	'A' THRU 'Z'	30	300	1	10	.110" - .130"
PCA11-A-J	'A' - 'J' [1 EA.]	30	300	1	10	.110" - .130"
PCA11-K-T	'K' - 'T' [1 EA.]	30	300	1	10	.110" - .130"
PCA11-U-Z	'U' - 'Z' [1 EA.] '-' [2 EA.] '+' [2 EA.]	30	300	1	10	.110" - .130"
PCA11-0 THRU PCA11-9	'0' THRU '9'	30	300	1	10	.110" - .130"
PCA11-0-9	'0' - '9' [1 EA.]	30	300	1	10	.110" - .130"
PCA11-MIN	'-'	30	300	1	10	.110" - .130"
PCA11-PLS	'+'	30	300	1	10	.110" - .130"

NOTES:

1. COLOR: WHITE WITH BLACK LEGENDS.
2. MILLIMETERS ARE IN [].



SYMBOLS ARE LOCATED ON BOTH SIDE OF MARKERS.

CAD FILENAME/LAYERS 100281DB-DC-C10351/04D

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PCA11-* CLIP-ON WIRE MARKER

3 3/28/11 RVU ADD '-' 2 EA. AND '+' 2 EA. '0'-'9', 'A'-'J', 'K'-'T' SHOULD BE [1 EA.].

2 8/11/10 RVU UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT.

1 10-06-06 RVU ADDED TOLERANCE AND REVISED TABLE.

0 9-12-06 RVU DRAWING RELEASE

REV DATE BY CHK DESCRIPTION

6336 R

6079 R

4881 R

3732 R

ECN - R CUST SUP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .062 (.XXX) ± .015
(.XX) ± .031 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU

DATE 10-14-04

CHK'D

MAT'L:

WHITE MARKER
-ACETAL

SCALE

DRAWING NO.

C10351

DWG
A
SIZE