

Datasheet

**RS Pro Stainless Steel Adjustable Height Mount 80mm
Rubber 20mm 500kg
RS Stock No: 283-1856**



Product Details

RS Pro stainless steel adjustable feet is designed to have a stabilizing and damping effect on installations of engineering machinery, scales and unsteady equipment. The design of the disc machine mount consists of a pressure plate made of galvanised sheet steel, which rests on a anti-vibration base element of impervious rubber. This simple yet functional design gives the mounts a very low installation height and a long service life.

Features and Benefits

- Damping machine mount for machines with built-in levelling screws
- Low installation height
- 500 kg static load capacity
- Rubber foot



ENGLISH

Specifications:

Base Material	Stainless Steel
Diameter	80 mm
Foot Material	Rubber
Overall Height	20 mm
Static Load Capacity	500 kg