

FEATURES

- Different types of screwlock assemblies for D sub connectors
- Thread size is 4-40 UNC
- Supplied disassembled

RS PRO Screwlock D Connector

RS Stock No.: 814-039



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO range of zinc plated screwlock assemblies for use with D-Sub connectors. The screwlock assembly kits in this range consist of three types; Male screwlock assembly which includes two clips and two locking screws. Female screwlock assemblies available in 8 mm thread length or 13 mm thread length which include locking screws, washers and nuts.

[829-918](#) – Male screwlock assembly

[814-023](#) – Female screwlock assembly 8 mm thread length

[814-039](#) – Female screwlock assembly 13 mm thread length

General Specifications

Accessory Type	Screwlock
For Use With	D Connector
Gender	Female
Finish	Zinc
Thread Size	4-40 UNC
Application	Preventing mechanical stress, provide EMI/RFI shielding and protection from the elements, Industrial, commercial and domestic applications and environments

Mechanical Specifications

Screw Length	13mm
---------------------	------

Approvals

Compliance/Certifications	ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007
----------------------------------	---

