



ATP CFast Card

Industrial Grade Flash Memory Cards

Targeted Product Portfolio, Engineered Specifically for Your Mission Critical Applications



ATP CFast cards combine the convenient and trusted format of CompactFlash with the speed, capacity and performance of SATA III, while maintaining backward compatibility with other SATA versions.

They are recommended as boot and storage devices in embedded and industrial applications such as avionics/aerospace, automation, marine navigation, telecommunication/networking and medical equipment where mission-critical data requires the highest level of reliability, durability and data integrity.

Special features and technologies include: PowerProtector, which provides a hardware-based backup power circuit during a power failure; Advanced Wear Leveling for higher endurance and longer product life span; ECC (error correction code) and AutoRefresh technologies, which correct and monitor the error bit levels to ensure data integrity in frequently read areas, and S.M.A.R.T. (Self-Monitoring, Analysis, and Reporting Technology) function for easy monitoring of various device health parameters to help predict storage failure for preventive action.

Key Features

- Advanced wear leveling algorithm
- Bad block management
- AutoRefresh technology
- PowerProtector
- S.M.A.R.T support

Applications

- Portable computation
- Automation
- Industrial PC
- Gaming
- On board data storage



Specifications

Product Name		CFast Card		
Product Line		Premium	Superior	
Naming		A800Pi	A600Si	A600Sc
Flash Type		SLC	iTemp MLC	MLC
Density		8 GB to 32 GB	16 GB to 128 GB	16 GB to 128 GB
Performance	Sequential Read up to (MB/s)	500	510	510
	Sequential Write up to (MB/s)	300	175	175
	Random Read IOPS up to	35,800	29,400	29,400
Interface		SATA III 6 Gb/s		
Operating Temperature		-40°C to 85°C	-40°C to 85°C	0°C to 70°C
Endurance	TBW* (max.)	2,667 TB	267 TB	320 TB
	MTBF @ 25°C	>2,000,000 hours		
Reliability of Insertions		10,000 minimum		
Dimensions: L x W x H (mm)		36.4 x 42.8 x 3.6		

* Under highest Sequential write value. May vary by density, configuration and applications.

Technologies & Add-On Services*		Life Monitor	Sudden Power-Off Recovery	Advanced Wear Leveling	AutoRefresh	Dynamic Data Refresh	Secure Erase	Industrial Temperature	Anti-Sulfur Resistors	Conformal Coating
Product Line	Premium	●	●	●	●	●	●	●	Δ	Δ
	Superior	●	●	●	●	●	●	Δ	Δ	Δ

Δ: Customization option available on a project basis.

To learn more about this product, contact your ATP Representative.

ATP Global Footprint

ATP TAIWAN(HQ)

TEL: +886-2-2659-6368
FAX: +886-2-2659-4982
sales-apac@atpinc.com

ATP USA

TEL: +1-408-732-5000
FAX: +1-408-732-5055
sales@atpinc.com

ATP EUROPE

TEL: +49-89-374-9999-0
FAX: +49-89-374-9999-29
sales-europe@atpinc.com

ATP JAPAN

TEL: +81-3-6260-0797
FAX: +81-3-6260-0798
sales-japan@atpinc.com

ATP CHINA

TEL: +86-21-5080-2220
FAX: +86-21-9687-0000-026
sales@cn.atpinc.com