



**Part Number :** [732870100](#)  
**Product Description :** SMA Attenuator, Plug to Jack, Straight, 18 GHz, 2 Watt, 10 dB, without Hex  
**Series Number :** 73287  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



## Documents & Resources

**Drawings**  
[732870100\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

|        |        |
|--------|--------|
| Status | Active |
|--------|--------|

|              |                                                                            |
|--------------|----------------------------------------------------------------------------|
| Category     | RF / Coaxial Connectors                                                    |
| Series       | 73287                                                                      |
| Description  | SMA Attenuator, Plug to Jack, Straight, 18 GHz, 2 Watt, 10 dB, without Hex |
| Keyword      | Attenuators                                                                |
| Product Name | SMA                                                                        |
| Style        | Attenuator                                                                 |
| Type         | Subminiature                                                               |
| UPC          | 198282460657                                                               |

## Electrical

|                           |        |
|---------------------------|--------|
| Attenuation Level (dB)    | 10     |
| Average Power Max (Watts) | 2      |
| Frequency                 | 18 GHz |
| Impedance                 | 50Ω    |
| VSWR (max)                | 1.35:1 |

## Physical

|                       |             |
|-----------------------|-------------|
| Body Style            | Without Hex |
| Gender                | Plug/Jack   |
| Keying to Mating Part | N/A         |
| Orientation           | Straight    |
| Packaging Type        | Bag         |
| Panel Mount           | No          |
| Panel Mount Method    | N/A         |
| PCB Mounting          | N/A         |
| Wire/Cable Type       | N/A         |