



Disco CCT 1



- Wall or ceiling light suitable for education and residential applications and ancillary areas
- All polycarbonate construction with opal diffuser and white trim ring
- CCT selectable between 3000K and 4000K
- Instant light output and unlimited switching

General Information

Lamp Type	LED
IP Rating	IP65
IK Rating	IK08
Class Protection	2
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	5
Material	Polycarbonate
Technical Information	
Wattage	8W
Lumens Delivered	670lm (4000K)





Lm/W	83lm/W (4000K)
Beam Angle	110
CRI	80
CCT	3000/4000K
Input	220/240V
Hertz	50/60Hz
Operating Temp	-10°C to 40°C
Lumen Depreciation	L70 60,000h
Power Factor	0.5



