

Features

- CCT & Wattage Adjustable LED Battens
- LED Battens Solution for Use in Commercial Settings
- Ultra-High Luminous Efficacy Of 150lm/W
- Cct Adjustable Between 3000k, 4000k and 6000k; Offering 4 Wattage Outputs
- Hands-Free Installation with Unique Hinged Locked Tray Design
- Supports Surface and Suspension Mounting With 20mm Knockout

RS PRO Batten Lights

RS Stock No.: 0286477



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO 6ft 20-38W CCT3 LED PRO Emergency Battens feature adjustable colour temperatures of 3000K, 4000K and 6000K and four wattage options, which make them an ideal solution for internal office, retail, healthcare or hospitality environments.

LED PRO Battens provide impressive luminous efficacy, achieving up to 150 lumens per watt (lm/W), making them an excellent choice for enhancing visibility while maximising energy savings. Furthermore, its hands-free flexibility supports effortless installation.

General Specifications

Lamp Type	Integrated Led
Luminosity	5130lm
Light source Luminosity	5700lm
Efficacy	120lm/W
Light Source Efficacy	150lm/W
Colour Temperature	3000K/4000K/6000K Selectable
Anti-Corrosive	No
Colour Tone	Warm White / Cool White / Daylight
Beam Angle	120°
LB70 Lifespan	50,000hrs
Colour	White body, Opal Diffuser
Emergency Duration	3hrs
Battery Type	LiFePO4, 1500mAh, 6.4V

Electrical Specifications

Wattage	20W/26W/32W/38W Selectable
Voltage Rating	220-240VAC
Frequency	50-60Hz
Sensor	No

Mechanical Specifications

Construction	Steel body, Polycarbonate diffuser
Length	1730mm
Width	60mm
Depth	75mm

Operation Environment Specifications

Operating Temperature Range	-10 to +40°
-----------------------------	-------------

Protection Category

IP Rating	IP20
IK Rating	IK08

Approvals

Standards Met	BS EN 60598-1
EU Energy Efficiency Rating	D