
























HMC Zyklop socket with 1/2" drive



Application: Hexagon headed bolts, screws and nuts

Design: Manual and (non-impact) machine applications, ball intercept ring, knurls at base for precision handling in manual operations, chrome vanadium, brushed chrome-plated finish. Colour coding to enable the desired bit socket to be easily located

							
		mm	mm	mm	mm	mm	mm
05003601001		10,0	37,0	15,5	24,0	17,0	
05003602001		11,0	37,0	16,5	24,0	17,0	
05003603001		12,0	37,0	17,5	24,0	17,0	
05003604001		13,0	37,0	19,0	24,0	17,0	
05003605001		14,0	37,0	20,0	24,0	17,0	
05003606001		15,0	37,0	21,0	24,0	17,0	
05003607001		16,0	37,0	22,5	24,0	17,0	
05003608001		17,0	37,0	24,0	26,0	17,0	
05003609001		18,0	37,0	25,0	26,0	17,0	
05003610001		19,0	37,0	26,5	26,0	20,0	
05003611001		20,0	37,0	28,0	26,0	20,0	
05003612001		21,0	37,0	29,0	26,0	20,0	
05003613001		22,0	37,0	30,5	26,0	20,0	
05003614001		24,0	37,0	33,0	28,0	20,0	
05003615001		27,0	40,0	36,5	32,0	23,0	
05003616001		30,0	42,0	40,0	34,0	25,0	
05003617001		32,0	42,0	42,0	36,0	25,0	
05003618001			3/8"	37,0	15,5	24,0	17,0
05003619001			7/16"	37,0	16,5	24,0	17,0
05003620001			1/2"	37,0	19,0	24,0	17,0
05003621001			9/16"	37,0	20,0	24,0	17,0
05003622001			11/32"	37,0	21,0	24,0	17,0
05003623001			3/8"	37,0	22,5	24,0	17,0
05003624001			11/16"	37,0	25,5	26,0	17,0
05003625001			3/4"	37,0	26,5	26,0	20,0
05003626001			7/8"	37,0	28,0	26,0	20,0
05003627001			15/16"	37,0	29,0	26,0	20,0
05003628001			1"	37,0	30,5	26,0	20,0
05003629001			1 1/16"	37,0	33,0	28,0	20,0
05003630001			1 1/8"	37,0	33,0	28,0	20,0
05003631001			1 1/4"	40,0	36,5	32,0	23,0
05003632001			1 3/16"	40,0	36,5	32,0	23,0
05003633001			1 1/2"	40,0	40,0	34,0	23,0
05003634001			1 3/4"	42,0	40,0	34,0	25,0
05003635001			1 7/8"	42,0	42,0	36,0	25,0