

Product information

10.8V Brushless Drill Driver CXT



Satisfying the professional's needs

DF332DZ

Voltage	10.8 v
Max. in wood	28 mm
Max. in steel	10 mm
Torque Settings	20 + Drill
Torque Settings; S/H Nm	21/35
Battery Type	Lithium-ion
Vibration: Drilling	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Noise sound pressure	72 dB(A)
Noise K factor	3 dB(A)
Body only machine	1
Net weight	1.2 kg
Chuck Capacity	0.8 – 10 mm
No Load Speed (Hi)	0 - 1,500 rpm
No Load Speed (Lo)	0 - 450 rpm



LITHIUM-ION



- Slide type Li-ion battery
- Brushless motor
- Electric brake
- 2 mechanical gears.
- Variable speed control by trigger
- Forward/reverse rotation
- Compact overall length of 154mm
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.
- Ergonomic soft grip
- Keyless Chuck
- LED job light
- Belt clip

Details correct as of: 13-10-2016

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com