


222A.T - Ground twist drills



Description:

- For steel up to 800 MPA, stainless steel, grey cast-iron and aluminium alloy.

	Length L [mm]	Weight [g]	Length [mm]
222A.T1	35.0	5.0	
222A.T1.5	40.0	5.0	
222A.T10	132.0	60.0	132.0
222A.T10.2	132.0	65.0	
222A.T10.5	132.0	70.0	
222A.T11	142.0	80.0	
222A.T11.5	142.0	90.0	
222A.T12	152.0	100.0	
222A.T12.5	152.0	110.0	
222A.T13	152.0	115.0	
222A.T2	50.0	5.0	
222A.T2.5	57.0	5.0	
222A.T3	62.0	5.0	
222A.T3.3	65.0	5.0	
222A.T3.5	70.0	5.0	
222A.T4	75.0	10.0	
222A.T4.2	75.0	10.0	
222A.T4.5	80.0	10.0	
222A.T5	85.0	10.0	
222A.T5.5	92.0	15.0	
222A.T6	92.0	15.0	
222A.T6.5	102.0	20.0	
222A.T6.8	105.0	25.0	
222A.T7	107.0	25.0	
222A.T7.5	110.0	30.0	
222A.T8	117.0	35.0	
222A.T8.5	117.0	40.0	
222A.T9	127.0	50.0	
222A.T9.5	127.0	55.0	

