

Product Family
Miller H500 series






Working at height can be a taxing job. Not only are construction workers generally at risk of serious injury or fatality, but long hours spent in a heavy, restrictive harness can be uncomfortable, painful, and cumbersome, leading workers to be less compliant and putting themselves more at risk.

The Honeywell Miller H500 Safety Harness synthesizes safety, quality, and comfort. Whereas other harnesses protect workers from serious injury at the expense of their long-term well-being, the Honeywell Miller H500 aims beyond compliance to keep workers safe and supported – making your job easier and keeping you safer.

The new Miller H500 range is available with shoulder/back padding, Mating buckles or Automatic Quick-release buckles



Product Numbers & Ordering Information

Product Numbers	Details
 1036081	Miller H500 Industry Comfort (IC6) with Shoulder/back pad Automatic buckles Front D ring. Size 1
 1036082	Miller H500 Industry Comfort (IC6) with Shoulder/back pad Automatic buckles Front D ring. Size 2
 1036083	Miller H500 Industry Comfort (IC6) with Shoulder/back pad Automatic buckles Front D ring. Size 3
 1036085	Miller H500 Industry Comfort (IC7) with Shoulder/back pad Automatic buckles Front web loops. Size 1
 1036086	Miller H500 Industry Comfort (IC7) with Shoulder/back pad Automatic buckles Front web loops. Size 2

Honeywell Miller H500 Harness



1036087

Miller H500 Industry Comfort (IC7)
with Shoulder/back pad Automatic buckles Front web loops. Size 3



1036109

Miller H500 Quick Fit (QF1)
with Mesh vest Automatic buckles Front web loops. Size 1



1036121

Miller H500 Quick Fit (QF1)
with Mesh vest Automatic buckles Front web loops. Size 2



1036122

Miller H500 Quick Fit (QF1)
with Mesh vest Automatic buckles Front web loops. Size 3



1036089

Miller H500 Industry Standard (IS1)
with Mating buckles. Size 1



1036090

Miller H500 Industry Standard (IS1)
with Mating buckles. Size 2



1036091

Miller H500 Industry Standard (IS1)
with Mating buckles. Size 3



1036093

Miller H500 Industry Standard (IS2)
with Automatic buckles. Size 1



1036094

Miller H500 Industry Standard (IS2)
with Automatic buckles. Size 2



1036095

Miller H500 Industry Standard (IS2)
with Automatic buckles. Size 3



1036097

Miller H500 Industry Standard (IS3)
with Mating buckles Front D ring Size 1



1036098

Miller H500 Industry Standard (IS3)
with Mating buckles Front D ring Size 2



1036099

Miller H500 Industry Standard (IS3)
with Mating buckles Front D ring Size 3

Honeywell Miller H500 Harness



1036101

Miller H500 Industry Standard (IS4)
with Automatic buckles Front D ring Size 1



1036110

Miller H500 Industry Standard (IS4)
with Automatic buckles Front D ring Size 2



1036111

Miller H500 Industry Standard (IS4)
with Automatic buckles Front D ring Size 3



1036113

Miller H500 Industry Standard (IS5)
with Mating buckles Front web loops. Size 1



1036103

Miller H500 Industry Standard (IS5)
with Mating buckles Front web loops. Size 2



1036104

Miller H500 Industry Standard (IS5)
with Mating buckles Front web loops. Size 3



1036106

Miller H500 Industry Standard (IS6)
with Automatic buckles Front web loops Size 1



1036107

Miller H500 Industry Standard (IS6)
with Automatic buckles Front web loops Size 2



1036108

Miller H500 Industry Standard (IS6)
with Automatic buckles Front web loops Size 3



1036123

Miller H500 High Visibility (HVY1)
with High Viz Yellow jacket Automatic buckles Front web loops. Size 1



1036124

Miller H500 High Visibility (HVY1)
with High Viz Yellow jacket Automatic buckles Front web loops. Size 2



1036125









Miller H500 High Visibility (HVY1)
with High Viz Yellow jacket Automatic buckles Front web loops. Size 3



1036126

Miller H500 High Visibility (HVY2)
with High Viz Yellow jacket Automatic buckles Front D ring. Size 1

Honeywell Miller H500 Harness

	1036127	Miller H500 High Visibility (HVY2) with High Viz Yellow jacket Automatic buckles Front D ring. Size 2
	1036128	Miller H500 High Visibility (HVY2) with High Viz Yellow jacket Automatic buckles Front D ring. Size 3
	1036129	Miller H500 High Visibility (HVO1) with High Viz Orange jacket Automatic buckles Front web loops. Size 1
	1036130	Miller H500 High Visibility (HVO1) with High Viz Orange jacket Automatic buckles Front web loops. Size 2
	1036131	Miller H500 High Visibility (HVO1) with High Viz Orange jacket Automatic buckles Front web loops. Size 3
	1036132	Miller H500 High Visibility (HVO2) with High Viz Orange jacket Automatic buckles Front D ring. Size 1
	1036133	Miller H500 High Visibility (HVO2) with High Viz Orange jacket Automatic buckles Front D ring. Size 2
	1036134	Miller H500 High Visibility (HVO2) with High Viz Orange jacket Automatic buckles Front D ring. Size 3

Overview

Key Features

- Light-weight and ergonomic
- Highly breathable shoulder/back padding
- Comfortable around the legs, waist, back, and shoulders
- Increased freedom of movement
- Smart rebar hook/lanyard keepers and SRL web link
- Side adjustment strap for better ergonomic fit - Quick and easy to fit and adjust
- Improved visible stitch pattern
- Fall-impact indicators

Benefits:

GREATER FREEDOM OF MOVEMENT

- New shoulder/back padding design minimises overhead muscular fatigue (overexertion)
- New specially formulated webbing flexes to accommodate movement and body contours for optimum comfort around legs and shoulders (6% stretch)
- New side-adjustment straps for better ergonomic fit
- H-Design leg design for greater user comfort

Honeywell Miller H500 Harness

- New side-adjustment straps for better ergonomic fit
- H-Leg design for greater user comfort

MORE BREATHABILITY

- Workers are kept drier and cooler with new "best in class" anatomically and ergonomically designed pressure-relief breathable shoulder/back padding

SMART & INTUITIVE FEATURES

- Smart anti-tangle for hassle-free donning experience
- Dedicated SRL web link for an easy attachment of personal SRLs
- User friendly Pull-Free Lanyard keepers allows users to attach lanyards when not in use
- Clearly identifiable fall impact indicators for hassle-free inspection
- Improved visible stitch pattern for easy inspection
- Lightweight aluminium Quick-release Cobra® buckles
- Highly visible protected label protection for hassle-free inspection
- Water repellent webbing
- Rated 140 kg (max weight capacity)

Recommended Industries/Use

- Construction
- Utilities

Hazards

- Fall from height

Regulations

- EN361 - :2002

Literature & Documents

HIS-FALL-H500-Harness-BRO-EN-A4-V3_0820_highres

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Fall_Protection/4295004838/1033.aspx

Technical Support

Technical Support

Northern and Central Europe Phone - +49 (0) 928/8302 – 205

Email – techniservnorth.hsp@honeywell.com

Southern Europe, UK & Ireland Phone - +33 (0) 2 48 52 40 4

Email – techniserv.hsp@honeywell.com