



DCF887NT

XR 18V 3 Speed BL Impact Driver Naked in TSTAK

Selling Proposition

- High power Brushless motor outputting up to 205Nm of torque ensures heavy applications are completed quickly
- Application control is achieved through 3 motor speeds and torque settings including PrecisionDrive
- PrecisionDrive mode offers additional control in screwdriving applications to avoid material and fastener damage
- Super lightweight and compact the tool is very comfortable to use and fits in small spaces
- 3x LED "Halo" light ring offers excellent workpiece lighting
- Compatible with all DEWALT 18V XR battery packs

Standard Equipment

- Belt hook
- Magnetic bit holder
- TSTAK compatible kitbox

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Battery chemistry	Li-Ion
Voltage	18 V
Battery Capacity	N/A Ah
Max Torque	205 Nm
Power Output	400 Watt
No Load Speed	0-1000, 0-2800, 0-3250 rpm
Impacts per Minute	0 - 3800 ipm
Bit Holder	6.35mm (1/4")