
54555

Special lamps for IR applications



Product benefits

- Rapid and precise temperature control
- Rapid reaction time for controlling the temperature
- Small space requirements
- Robust design

Product features

- Can be supplied in clean-room packaging




Technical data

Electrical data

Nominal wattage	1000.00 W
Nominal voltage	120 V
Construction voltage	120 V

Dimensions & weight



Light center length (LCL)	60.3 mm
Diameter	20.0 mm
Length	101.0 mm

Lifespan

Lifespan	300 h
----------	-------

Additional product data

Base (standard designation)	G9.5 ¹⁾
-----------------------------	--------------------

¹⁾ Ceramic base

Capabilities

Burning position	Any
------------------	-----

Country specific categorizations

ANSI code	-
-----------	---

Product datasheet

Safety advice

These lamps emit UV radiation and reach a high internal pressure during operation. These lamps may only be operated in enclosed casings specially designed for the purpose. If used incorrectly, UV radiation may lead to sunburn and conjunctivitis. Read the enclosed safety instructions before use.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321216304	54555	Folding carton box 1	48 mm x 41 mm x 129 mm	0.25 dm ³	52.00 g
4008321216311	54555	Shipping carton box 12	133 mm x 142 mm x 168 mm	3.17 dm ³	650.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.