

### General Information

Extended Product Type:	JSTD20B
Product ID:	2TLA020007R2100
EAN:	7350024460179
Catalog Description:	JSTD20B Twohand with Emergency Stop
Long Description:	Two-hand device with conventional operating buttons and E-stop button. Operating push buttons are 60mm in diameter, black, 9N operating force, 1 NO + 1 NC contacts, rated current of 10A. E-stop button diameter is 40mm, 40N operating force, 2 NC positive opening contacts, rated current of 10A. Buttons are mounted in black painted steel housing designed for two-hand applications, IP65. Terminal blocks within housing for connection to buttons. Highest level of safety can be achieved when using in conjunction with a JSBR4 safety relay for two-hand buttons and RT9/RT6 safety relay for e-stop button or a Pluto Safety PLC.

### Categories

Products » Low Voltage Products and Systems » Control Products » Safety Products » Safety Control Devices

### Ordering

EAN:	7350024460179
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365011

### Dimensions

Product Net Width:	0.490 m
Product Net Height:	0.145 m
Product Net Depth:	0.170 m
Product Net Weight:	0.640 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Gross Weight:	5.5 kg

### Safety Information

Performance Level (PL):	Up to e
Safety Category Acc. to ISO 13849-1:	4

### Additional Information

Product Main Type:	JSTD20
Product Name:	Two Hand Safety Control Device

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2TLC172001C0202_chapter10
Declaration of Conformity - CE:	2TLC172023D0201

### Classifications

ETIM 4.0:	EC001260 - Two-hand control device
ETIM 5.0:	EC001260 - Two-hand control device
Object Classification Code:	B

No image available