



50569-961 Polo shirt

Premium Performance - Modern fit

MASCOT® UNIQUE



60% cotton/40% polyester
210 g/m²



Pique fabric.

Industrial care category A1

Certifications



Logo

Logo placement:

- Workwear logo. Left breast. Max 12x10 cm/4.7x3.9 inches
- Workwear logo. Vertical on left breast, read from the top downwards. Max 28x8 cm/11x3.1 inches
- Workwear logo. Vertical on left breast, read from the bottom upwards. Max 28x8 cm/11x3.1 inches
- Workwear logo. Right breast. Max 12x10 cm/4.7x3.9 inches
- Workwear logo. Vertical on right breast, read from the top downwards. Max 28x8 cm/11x3.1 inches
- Workwear logo. Vertical on right breast, read from the bottom upwards. Max 28x8 cm/11x3.1 inches
- Workwear logo. Mid-back. Max 28x28 cm/11x11 inches
- Workwear logo. On the nape. Max 12x5 cm/4.7x1.9 inches
- Workwear logo. Special placement. Contact to discuss further



- Good space for placement of company logo.
- Modern, close fit with great freedom of movement.
- Ribbed collar.
- Buttoned placket.
- Extra padding over the seam at the neck so the seam does not cause irritation.

Technical info

Two-toned. Modern fit. Strong quality. Ribbed collar and cuffs. Buttoned placket. Neckband.

User

