

## Datasheet

# 4 Gang Trailing Socket

RS Stock number: 249-4536



### Description:

BS1363 surge protected range is an ideal solution for home, office and industrial use. The ruggedized ABS plastic or Aluminium cases ensure a high impact resistance and long working life. The internal surge suppressors are tested against 'worst case' conditions, as defined in International Standards IEEE C62.41-1991 Cat B3 and comply with the recommendations of BS6651:1999 Annex C.

### Specifications:

Voltage Rating (Nominal): 230V rms  
Maximum Current Rating: 13A (7A Fuse fitted)  
Power Consumption: Negligible  
Lead Length: 2m  
Surge Handling (8/20us) [Per Element]: 13.5kA [4.5kA]  
Voltage Protection Level (Up) 8/20us: 900V@3kA 8/20us  
Response Time: <10ns  
BS6651:1999 Annex C Location Category: A & B

### Standard Features:

- Red status indicator to show mains power/fuse OK.

### Options:

- 2, 4 or 6 way.
- Choice of Fire retardant ABS or Aluminium case.
- Choice of standard BS 1363 or RCD plug.
- Various additional features.