



ENGLISH

Datasheet

Stock No: 379-3733

RS Pro Plastic Cable Dispenser, 115 m, 30 m, 33 m Maximum Cable Length 300mm dia.



Product Details

Audio Cable Reels

Heavy-duty cable drums, a polypropylene type (CR-P) and a steel type (CR-S). Both models are mounted on a rugged tubular steel frame and have a friction brake with an integral winding handle.

Features and Benefits

- An internal clamp provides strain relief and anchors the cable in the hub
- The large hub diameter ensures that the minimum bend radius of the cable is not exceeded when wound onto the reel, thus protecting the cable and preventing kinking
- The CR-P models are made from high impact polypropylene with a removable side flange that can be cut to accept panel mount connectors
- The CR-S models are made of steel with a removable plastic hub plate that can easily be cut to accept panel mount connectors

Stock No.	Size (mm)	Material	Colour	Maximum cable capacity (m) for Cable OD:		
				6.5mm	12mm	14mm
379-3727	240	Plastic	Red	60m	25m	20m
379-3733	300	Plastic	Orange	115m	33m	30m
379-3705	380	Steel	Blue	215m	65m	55m
379-3755	460	Steel	Blue	350m	110m	90m

Note

Cable to be ordered separately

Reels, Racks and Stands



Specifications

Type	Reel
Maximum Cable Length Capacity	30 m, 33 m, 115 m
Cable Diameter Capacity	6.5 mm, 12 mm, 14 mm
Height	30mm
Width	100 mm
Diameter	300mm
Material	Plastic