

M18 ONEPD-502X | ONE-KEY™ FUEL™ percussion drill

Article: 4933451147



- M18 FPD but with ONE-KEY™ technology.
- More power - unmatched torque of 135 Nm.
- More speed - delivers up to 2000 rpm.
- Electronic clutch with 13 torque settings.
- Flexible battery system: works with all Milwaukee® M18™ batteries.
- Connect via Bluetooth® with the Milwaukee® ONE-KEY™ app.
- Complete tool customisation via ONE-KEY™ app to tune the tool to your needs.

	M18 ONEPD-502X
Sound pressure level (dB(A))	99.9
Sound pressure level uncertainty (dB(A))	3
Sound power level measured (dB(A))	110.9
Sound power level measured uncertainty (dB(A))	3
Vibration screw driving (m/s ²)	1.33
Vibration screw driving uncertainty (m/s ²)	1.5
Vibration drilling into Metal [m/s ²]	1.29
Vibration drilling into metal uncertainty [m/s ²]	1.5
No load speed gear 1 (rpm)	0 - 550
No load speed gear 2 (rpm)	0 - 2000
Max. torque (Nm)	135
Vibration percussion drilling into concrete [m/s ²]	13.2
Vibration percussion drilling into concrete uncertainty [m/s ²]	1.5
Voltage (V)	18
Battery pack capacity (Ah)	5.0
Battery type	Li-ion
Max. percussion rate (bpm)	0 - 32,000
Supplied in	HD Box
Charger supplied	59 min
No. of batteries supplied	2
Article Number	4933451147
Weight with battery pack (kg)	2.5
Max. drilling steel (mm)	13