





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	RELEASED PER EC 0S13-0087-05	08SEP05	GP	JG



- 1 HOUSING: BLACK POLYESTER, UL 94V-0 RATED.
CONTACTS: PHOSPHOR BRONZE.
- 2 GOLD FLASH FOR A LENGTH OF 2.54[.100] MIN FROM
MATING END, 2.54 μm [.000100] MIN TIN FOR A LENGTH OF
3.18[.125] FROM OPPOSITE END, ALL OVER 1.27 μm [.000050]
MIN NICKEL.
- 3 0.76 μm [.000030] MIN GOLD FOR A LENGTH OF 2.54[.100] MIN FROM
MATING END, 2.54 μm [.000100] MIN TIN FOR A LENGTH OF
3.18[.125] FROM OPPOSITE END, ALL OVER 1.27 μm [.000050]
MIN NICKEL.



RECOMMENDED PC BOARD MOUNTING DIMENSIONS

**COPYRIGHT 2005
TYCO ELECTRONICS CORP
ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. PETERS 08SEP05		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK S. BOLASH 08SEP05			
DIMENSIONS: INCHES		APVD M. WALMSLEY 08SEP05		NAME	
		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		RECEPTACLE ASSEMBLY, SIZE 3, 25 POSN, VERTICAL, AMPLIMITE HD-20	
MATERIAL		APPLICATION SPEC —		SIZE	CAGE CODE
		WEIGHT —		DRAWING NO	
FINISH				A2 00779 C=5207828	
CONTACTS: SEE TABLE		CUSTOMER DRAWING		SCALE	SHEET
				4:1	1 of 1
				REV	0