



Main

Range of product	Modicon Quantum automation platform
Product or component type	Ethernet network TCP/IP module
Concept	Transparent Ready
Web server	Class B30
Web services	Data Editor (via PC terminal) Diagnostics via predefined web pages Rack viewer
Communication service	Bandwidth management FDR server Global Data I/O scanning Modbus TCP messaging SNMP network management
Communication port protocol	Ethernet Modbus TCP/IP
Physical interface	MT/RJ 100BASE-FX fiber optic RJ45 10BASE-T/100BASE-TX twisted pair
Transmission rate	10/100 Mbit/s

Complementary

Redundancy	Yes hot standby redundant architecture
Supply	Via the power supply of the rack
Marking	CE
Local signalling	1 LED 10 Mbps or 100 Mbps data rate (10 MB/100 MB) 1 LED collision detection (Coll) 1 LED download mode (Kernel) 1 LED Ethernet module fault (Fault) 1 LED Ethernet network status (RUN) 1 LED full-duplex mode (Fduplex) 1 LED module ready (Ready) 1 LED network active (Link) 1 LED rack operational (Active) 1 LED transmission/reception activity (TxAct/RxAct)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Current consumption	750 mA 5 V DC
Module format	Standard
Product weight	0.345 kg

Environment

IP degree of protection	IP20
Product certifications	CUL UL 508
Standards	CSA C22.2 No 142 FM Class 1 Division 2
Resistance to electrostatic discharge	4 kV contact IEC 801-2 8 kV on air IEC 801-2
Resistance to electromagnetic fields	10 V/m 80...1000 MHz IEC 801-3
Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	95 % without condensation
Operating altitude	<= 4500 m

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0827 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------

Racks for Modules Mounting

Dimensions of Modules and Racks

- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots