



## PSC-2 0560

E1441384

Splicing Connector, 2-Conductors, 0.5-6.0mm<sup>2</sup>, AWG 20-10, with Lever



### Product Properties:

Number of clamp positions (device side)	2 .
Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	40 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	2 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	12-14 mm
Colour	Green
Operating temperature	-40-105 °C
Connector type	Topplämna, öppningsbar
Flammability rating (UL94)	V2

### Dimensions:

Max. AWG-size	10
Min. AWG-size	20
Nominal cross section (device side)	0.5-6 mm <sup>2</sup>
Nominal cross section (installation side)	0.5-6 mm <sup>2</sup>

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-6 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.5-6 mm <sup>2</sup>
Width	21 mm
Height	11 mm
Strip length	12-14 mm
MOQ	50 .
Unit	pcs
Nominal cross section	0.5-6 mm <sup>2</sup>
Length	16 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

### **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	102017
Search Description	ENR2026V, EFO2026V, SKV2026MK
Alternative SKU	PSC-20560
E-no	E1441384

### **Logistic information:**

Barcode	733117643255
Country of origin	CN
E-no	E1441384
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	50 .
Stock code	PSC-2 0560
Taric code	85369010
Unit	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.

---

**Nelco Contact AB** - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - [order@nelco.se](mailto:order@nelco.se) - [www.nelco.se](http://www.nelco.se)