



Part Number : 1731110185

Product Description : FCT Metal Backshell for D-Sub Connector, Shell Size 2, Straight Cable Outlet, Extra Large Inner Chamber, with Double Cable Clamps and #4-40 Locking Screws



Series Number : 173111

Status : Active

Product Category : D-Sub Backshells

Engineering Number : FMK2GL

Documents & Resources

Drawings

[1731110185_sd.pdf](#)

3D Models and Design Files

[1731110185_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Metal Backshell for D-Sub Connector, Shell Size 2, Straight Cable Outlet, Extra Large Inner Chamber, with Double Cable Clamps and #4-40 Locking Screws
Magnetic	Yes
Product Name	FCT Products
Type	Rugged Metal
UPC	889056864640

Electrical

Shielded	Yes
Shield Type	Solid Metal

Physical

Cable Diameter	max. 10.00mm
Material - Backshell	Zinc Die-cast
Material - Screw	Steel
Mounting Style	Locking Screw
Net Weight	75.000/g
Orientation	Straight
Packaging Type	Carton
Plating - Backshell	Nickel
Temperature Range - Operating	-35° to +100°C

Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 2

This document was generated on Jul 10, 2025