

Datasheet

Stock No: 215-5708

ENGLISH

RS Pro 47µF 35 V dc Aluminium Electrolytic Capacitor 1000h 8 (Dia.) x 11.5mm



Product Details:

ARD (ROD) Series Starget

- Audio grade polarised electrolytic capacitors specifically designed for use where high performance and minimum distortion are required
- Oxygen-free copper lead-out wires

Capacitance Tolerance (%)	20
Operating Temperature (°C)	-40 → +85
Life Expectancy	1000 hrs at 85°C
Leakage current	0.01 CV or 3 µA whichever is greater

Note

These Capacitors are Polarised



ENGLISH

Specifications:

Capacitance	47μF
Technology	Electrolytic
Voltage	35 V dc
Dimensions	8 (Dia.) x 11.5mm
Height	11.5mm
Diameter	8mm
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+85°C
Lead Pitch	3.5mm
Construction	Radial
Series	ARD (ROD)
Terminal Type	Through Hole
Tolerance Plus	+20%
Lead Diameter	0.6mm
Leakage Current	4 μΑ
Lifetime	1000h
Ripple Current	120mA
Tolerance Minus	-20%
Tolerance	±20%