

Features

- **Specially Designed for Schneider Merlin Gerin Breakers** – Ensures a precise and secure fit for moulded circuit breakers.
- **Dual-Locking Mechanism** – Enhances safety by providing added locking assurance during maintenance.
- **Supports Up to 3 Padlocks** – Accommodates padlocks with shackle diameters up to 7.5 mm for group lockout procedures.
- **Tool-Free Installation** – Simple three-step setup for fast and efficient deployment.
- **Blocks Switch Toggle Operation** – Engages directly behind the breaker toggle to prevent accidental reactivation.
- **Compact & Portable** – Easily stored or carried for quick access in field or maintenance settings.

RS PRO Two Way Black MG Toggle Hasp

RS Stock No.: 0710520



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Designed specifically for locking out Schneider Merlin Gerin moulded circuit breakers.*
- *Constructed from mild steel for strength and durability in industrial settings.*
- *Dual-locking slots allow two locking points, ensuring higher lockout security.*
- *Allows up to 3 padlocks to be attached, effectively securing energy isolation points.*
- *Installation is quick and requires no tools—simply position, insert, and lock.*
- *Prevents accidental energization by locking the breaker toggle in the OFF position.*
- *Compact size makes it convenient to carry and ideal for toolkits or maintenance bags.*

General Specifications

Type	Lockout Hasp
Material	Black powder coated mild steel and aluminium rivet.
Colour	Black
Padlock holes	03
Package	PE-LD

Mechanical Specifications

Dimensions	37mm x 49mm x 7mm
Length	37mm
Height	49mm
Depth	7mm
Maximum Shackle Diameter	7.5mm
Weight	32 Grams

Operation Environment Specifications

Withstand temperature	-30°C to 90°C
-----------------------	---------------