

Heavy-duty neoprene gloves, designed with a double-insulating liner to resist extreme temperatures

- **Specialized protection:** AlphaTec® 19-026 neoprene gloves feature a double-insulating thermal liner, for heightened protection against thermal risks and hazards, including intermittent heat contact up to 180°C/356°F
- **Advanced defenses:** Unaffected by cleaning solutions and detergents, these AlphaTec® gloves' neoprene coating ensures advanced chemical resistance, offers mechanical protection and withstands oils and greases
- **Enhanced flexibility and grip:** In addition, they are flexible and offer excellent grip performance, ensuring secure handling and assured dexterity

Industries

- Machinery and Equipment
- Metal fabrication
- Chemical
- Automotive Aftermarket

Applications

- Press work
- Handling materials with sharp or rough edges
- Production line support & maintenance
- Unexpected leakages spills or other releases



Previously known as: Scorpio™ 19-026

Key Features

- **Double-insulating thermal liner:** Resistance to both hot and cold*
- **High-grade neoprene coating:** Excellent chemical and mechanical protection
- **Flexible, grip-enhancing design:** Greater dexterity, more secure handling

*protection from intermittent contact with hot surfaces up to 180°C/356°F



Vulcanization Chemical Accelerators

- Diphenyl guanidine
- Diphenyl thiuram urea

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



CE 0493

EN388: 2016



3122B

EN 511



121

EN ISO 374-1:2016



AKLMPT

EN ISO 374-5:2016



EN 407



32XX4X

Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 19-026	Liner Material: Double insulating liner, Cotton Coating Material: Neoprene	8, 10	660 / 26	Black	1 pair in a bag; 12 bags in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.