



Product data sheet

Power tools for trade & industry

Cordless Ratchet Wrench

PRO GRC 12V-60 3/8 SN



Compact ratchet wrench handles screws in tight spaces with ease

The most important data

Battery voltage	12.0 V
Torque, max.	60 Nm

Part Number 0 601 9N8 301

Technical data

Technical data

Weight excl. battery	0.76 kg
Torque, max.	60 Nm
Battery voltage	12.0 V
Packaging dimensions (width x length x height)	208 x 340 x 98 mm
Torque, max. (hard screwdriving applications)	60 Nm
Weight incl. battery	0.95 kg
BITURBO	No

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Outstanding tool control and comfortable grip thanks to ergonomic design and small circumference
- Compact and convenient with lean 12 V system for accessing tight spaces and LED light to illuminate dark areas
- Efficient, intuitive operation thanks to variable speed trigger
- Robust and durable thanks to metal housing

**HEAVY
DUTY**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

